



MSA	Voltage	Size	Kg
06.210	220 V / 50 Hz	450 x 280 x 270 mm	17.500
06.210-110	110 V / 60 Hz	450 x 280 x 270 mm	17.500

Semi-automatic glass cutting machine for flat and domed glasses : tempered mineral, synthetic and unbreakable sapphire.

Delivered with :

- 1 bottle of emulsified oil K3, 250 ml
- 1 bottle of lubricating oil K4, 100 ml
- 1 corundum stone K5, 100 x 10 mm
- 1 glass centring tool
- 1 glass holder
- 3 "L" Allen wrenches (2, 2.5 and 4 mm)
- 1 forked wrench (8-10 mm).

Accessories :

MSA	Item	Kg
06.210-A	Complete bloc "A"	1.600
06.210-B	Complete auxiliary motor	14.000
06.301-A	Resin cast, 500 g	0.560
06.301-B	Resin cast, 1000 g	1.020
06.302-A	Hardening liquid, 250 ml	0.450
06.302-B	Hardening liquid, 500 ml	0.860
06.303-A	Emulsified oil K3, 250 ml	0.315
06.303-B	Emulsified oil K3, 1000 ml	0.920
06.305	Corundum stone K5 A0220, 100 x 10 mm	0.018
06.306	Lubricant oil K4, spray 100 ml	0.120
06.310	Support plate for domed glasses	0.150
06.311-A	External green belt	0.007
06.311-B	internal red belt	0.010
06.312	Roughing grinding wheel	0.095
06.313-A	Internal bevelling wheel	0.065
06.313-B	External bevelling wheel	0.065
06.314	Exterior bevelled polishing wheel	0.065
06.315	Complete assortment of 4 grinding wheels	0.290